

## UV-4C Microprocessor Integrator

(also available for LED measurement up to 20 W/cm<sup>2</sup>)

- + UV-A intensity mW/cm<sup>2</sup> + UV-A dose mJ/cm<sup>2</sup>
- + UV-B intensity mW/cm<sup>2</sup> + UV-B dose mJ/cm<sup>2</sup>
- + UV-C intensity mW/cm<sup>2</sup> + UV-C dose mJ/cm<sup>2</sup>
- + UV-V intensity mW/cm<sup>2</sup> + UV-V dose mJ/cm<sup>2</sup>
- + Full UV intensity mW/cm<sup>2</sup> + Full UV dose mJ/cm<sup>2</sup>
- + Permanent or triggered recording\*
- + temperature measuring (option)
- + SD Memory Card (option)
- + graphical and numerical display on a PC (option)
- + re-chargeable accu cell
- + further spectral ranges upon request
- + available up to 20W/cm<sup>2</sup>
- + available with high speed sampling rate 0.0007s(1400/s)



The UV-4C Microprocessor Integrator is a self-contained, high quality UV measuring instrument. It is designed to measure, record and display peak UV intensity and UV dosage in the UV curing process.

It is equipped with four different UV sensors for the individual measuring of

**UV-A 315 – 410 nm**  
**UV-B 280 – 315 nm**  
**UV-C 230 – 280 nm**  
**UV-V 395 – 445 nm**  
**UV - 250 – 410 nm**

With these four different UV-bands all of the measuring requirements of UV curing applications can be covered.

Due to its four different UV sensors and the integrated microprocessor the UV-4C can measure, record and display the peak of the UV-energy (mW/cm<sup>2</sup>) for each UV-band individually plus the peak of total UV energy. Additionally, this UV-Integrator is calculating the UV-dosage (mJ/cm<sup>2</sup>) of the UV energy supplied during the time of exposure of one measuring cycle. The UV-dosage is calculated for each UV-band (UV-A, UV-B, UV-C and UV-V) individually and as total Integral of UV-dosage over all three UV-bands.

This allows to determine not only the total energy, but also how that energy is delivered, i.e., what intensity and dose at what UV-band.

The four sensors are on the back of the unit which also serves as a heat shield. After completion of the measuring cycle all measuring results can be scrolled through on the built in 2 x 16 digit LCD display. A special AUTO-OFF feature that turns off the unit automatically after one minute serves as energy saving and extension of the battery service life.

\*This Microprocessor Integrator features a selectable „triggered mode“, i.e. the 30 sec recording cycle starts within a 120 second readiness phase not before the incident UV-intensity exceeds 2 mW/cm<sup>2</sup>.

As an option, this microprocessor integrator is available with an SD-Memory Card Slot and an evaluation software for downloading the data to a computer to show, edit and store a history of the measuring results of the entire measuring cycle as graphic charts (mW/cm<sup>2</sup>) and (mJ cm<sup>2</sup>)

### Item 2.7. UV-4C Microprocessor Integrator

\*also available in other spectral range combinations upon request

Subject to change without prior notice © 2014-01

UV-DESIGN (Office)  
Triebstrasse 3  
63636 Brachtal  
GERMANY  
Tel.: +49 (0)6053 619824  
Fax: +49 (0)6053 619820

(Office & Workshop) UV-DESIGN  
Fabrikstrasse 12  
63636 Brachtal  
GERMANY  
Tel.: +49 (0)6053 8095431  
Fax: +49 (0)6053 8095433



## UV-4C Microprocessor Integrator

### Technical Data:

Spectral ranges:	UV-A 315 – 410 nm UV-B 280 – 315 nm UV-C 230 – 280 nm UV-V 350 – 460 nm UV 230 – 410 nm
Max. Power Input*:	0 to 2,000 mW/cm <sup>2</sup>
Measuring range:	0 to 2,000 mW/cm <sup>2</sup>
Sampling rate:	0.01 sec (100/sec)
Recording cycle:	90 sec.
Readiness phase:	120 sec.
Display range:	0 to 36,000 mJ/cm <sup>2</sup>
Display:	LCD, 2 x 16 digits
Power source:	3.7 V LiPO Accu
Power consumption:	20 $\mu$ A
Accu service life:	1,000 re-charging cycles
Dimensions:	$\varnothing$ 5.5" (140 mm), height 1/2" (13 mm)
Weight:	approx. 17.5 ounce (500 g)
Operating temperature:	32° to 113° F / 0 to 45° C
Heat protection:	Heat shield on back plate
Base Accuracy:	$\pm$ 5 %

### OPTION: SD-Memory Card

**Option:  
Graphic Chart:**  
With SD Card slot.  
Stores data to an  
SD-Memory card  
For transmission to  
a computer



While on the conveyer belt, the UV-4C Microprocessor Integrator can withstand max. 230° F / 110° C for up to 10 seconds. The temperature of the housing should not exceed 113° F / 45° C.

Because of uneven radiation distribution of the UV light source and different type of construction of the measuring devices by different manufacturers, different readings may appear under the same measurement conditions.

### Calibration:

In order to keep its full function and precision it is recommended to have re-calibration done once per year. Re-calibration will also be necessary after change of battery. Ongoing, PTB traceable calibration with certificate

**Warranty:** 2 years from the date of purchase

**\*also available up to 20W/cm<sup>2</sup>, display resolution in relation to maximum wattage**

**\*also available with high speed sampling rate 0.0007s(1400/s)**

Subject to change without prior notice © 2014-01

UV-DESIGN (Office)  
Triebstrasse 3  
63636 Brachtal  
GERMANY  
Tel.: +49 (0)6053 619824  
Fax: +49 (0)6053 619820

(Office & Workshop) UV-DESIGN  
Fabrikstrasse 12  
63636 Brachtal  
GERMANY  
Tel.: +49 (0)6053 8095431  
Fax: +49 (0)6053 8095433